

Hose sleeve

ST G1/8-AG 9 MS-V

Part no...:10.08.03.00155

<https://www.schmalz.com/10.08.03.00155>


Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G1/8-AG 9 MS-V

Hose sleeve



Thread G1: G1/8"-M
Hose diameter (rec.) d: 9 mm
Material: Brass
Surface: nickel plated
Length L: 5 mm
Nominal diameter dn: 4 mm

Design Data



Attribute	Value
dn	4 mm
D	8.30 mm
G1	G1/8"-M
L	5 mm
L1	34 mm
LG1	8 mm
SW1	14 mm

Technical Data

Attribute	Value
Material	Brass
Weight	19 g

Accessories

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Hose sleeve

ST G1/8-AG 9 MS-V

Part no...:10.08.03.00155

<https://www.schmalz.com/10.08.03.00155>



VSL 12-9 PE BL

Part no...:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no...:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



VSL 15-9 PVC-G KL-TR

Part no...:10.07.09.00005

External diameter D: 15 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx