

## Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 14-11 PU MI-TR

### Hose for vacuum and compressed-air systems



External diameter D: 14 mm

Internal diameter d: 11 mm

Length max.: 50 m


Material hose: PU

Bending radius min.: 100 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

### Design Data



| Attribute | Value |
|-----------|-------|
| d         | 11 mm |
| D         | 14 mm |

### Technical Data

| Attribute                           | Value               |
|-------------------------------------|---------------------|
| Hose type                           | 14-11               |
| Pressure range (operating pressure) | -0.95 ... 10.00 bar |
| Operating temperature               | -20 ... 90 °C       |
| Bending radius min.                 | 100 mm              |
| Length max.                         | 50 m                |
| Weight/Meter                        | 69 g/m              |
| Weight/Meter                        | 0.07 kg/m           |
| Material hose                       | PU                  |

### Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26  
[schmalz@schmalz.com.mx](mailto:schmalz@schmalz.com.mx)

## Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no...:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

### Accessories



#### KAPP 9 Band

Part no...:20.12.01.00036

Length L: 9 mm

Size: Band



#### SSB 10-16 ST-VZ

Part no...:10.07.10.00001

Clamping range: 10.0 ... 16.0 mm

Material: Steel

Surface: galvanised



#### STV-GE G1/2-AG 14

Part no...:10.08.02.00300

Thread G1: G1/2"-M

Hose diameter: 14 mm

Material: Brass

Operating temperature: °C

External diameter D: 21.5 mm

Length L: 25 mm

### Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26  
schmalz@schmalz.com.mx

## Vacuum hose (meter)

VSL 14-11 PU MI-TR

Part no.:10.07.09.00038

<https://www.schmalz.com/10.07.09.00038>



### STV-GE G3/8-AG 14

Part no.:10.08.02.00211

Thread G1: G3/8"-M

Hose diameter: 14 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 21.5 mm

Length L: 30.5 mm



### SVB-T 14

Part no.:10.09.02.00046

Hose diameter: 14 mm

Material: Brass

Operating temperature: °C

Length L: 72 mm

## Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26  
schmalz@schmalz.com.mx