

Suction cup (round)

SAUG-SCG 20 SI-HD-65 602 B

Part no...:10.01.30.01099

<https://www.schmalz.com/10.01.30.01099>

Home > Suction Cups for Flow Grippers SCG > SAUG-SCG 20 SI-HD-65 602 B

Suction cup (round)



Size: 20


Height H: 22.5 mm

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
D1	23 mm
Dmax (N)	39.60 mm
Dmax(S)	25 mm
dn	15 mm
Ds	21.50 mm
G1	M37x1-F
H	22.50 mm
LG1	5 mm
Z (Stroke)	3 mm

Technical Data

Attribute	Value
Size	20
Pressure range (operating pressure)	bar
Operating temperature	°C
Number of folds	1.50
Weight	15.40 g
Holding force	N
Air consumption	m³/h
Air consumption	l/min
Material hardness [Shore A]	65 Shore A

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Suction cup (round)

SAUG-SCG 20 SI-HD-65 602 B

Part no...:10.01.30.01099

<https://www.schmalz.com/10.01.30.01099>

Suction rate	m ³ /h
Suction rate	l/min
Suction cup material	Silicone SI-HD
Product family	SAUG-SCG

Spare parts



BCG 20 SI-HD-65 SC085

Part no...:10.01.06.04845

Size: 20

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx