

Vacuum lifting cylinder

HS 28-32 G1/8-IG

Part no...:10.01.07.00001

<https://www.schmalz.com/10.01.07.00001>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Vacuum Lifting Cylinders > Vacuum Lifting Cylinders HS > HS 28-32 G1/8-IG

Vacuum lifting cylinder for rapid separation of paper and plastic film




Stroke Z: 28 mm

Vacuum connection: G1/8"-F

Suction cup connection: G1/8"-F

Design Data



Attribute	Value
D	50 mm
D1	14 mm
G1	G1/8"-F
G2	G1/8"-F
G3	M8-F
G4	M8-F
H	97 mm
H1	67 mm
H2	10 mm
H3	10 mm
L	50 mm
LG1	8 mm
LG2	10 mm
LG3	12 mm
LG4	12 mm
Z (Stroke)	28 mm

Technical Data

Attribute	Value
Holding force	9 N
Air consumption	66.70 l/min

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx



Vacuum lifting cylinder

HS 28-32 G1/8-IG

Part no.:10.01.07.00001

<https://www.schmalz.com/10.01.07.00001>

Air consumption	4.00 m ³ /h
Cycle time	0.80 s
Weight	0.36 kg
Product family	HS

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx