

Basic Ejector

SBP HV 2 16 22 KU

Part no.:10.02.01.01961

<https://www.schmalz.com/10.02.01.01961>


[Home](#) > [Vacuum Technology for Automation](#) > [Vacuum Components](#) > [Vacuum Generators](#) > [Basic Ejectors](#) > [Basic Ejectors SBP-HV/HF With Plastic Main Body](#) > [SBP HV 2 16 22 KU](#)

Basic ejector for universal use



Shape: High Vacuum
Number of stages: 2
Nozzle diameter: 1.6 mm
Size: 22
Degree of evacuation: 90 %
Suction rate (max.): 159 l/min
Air consumption suction: 103 l/min
Material: Plastics

Design Data



Attribute	Value
B	31.50 mm
d2	6.20 mm
D	20 mm
G1	G1/4"-F
G2	G3/8"-F
G5	M6-F
H	45 mm
H2	6.50 mm
H3	22.50 mm
L	80 mm
L1	131 mm
L2	24.50 mm
L3	26.50 mm
L4	113 mm
SW2	12 mm
X1	22 mm
X2	26 mm
Y1	22 mm

Technical Data

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 5211
schmalz@schmalz.com.mx

Basic Ejector

SBP HV 2 16 22 KU

Part no.:10.02.01.01961

<https://www.schmalz.com/10.02.01.01961>

Attribute	Value
Nozzle diameter	1.60 mm
Number of stages	2
Degree of evacuation	90 %
Suction rate (max.)	159 l/min
Air consumption suction	6.34 m³/h
Air consumption suction	103 l/min
Sound level free	87 dB(A)
Sound level suction	76 dB(A)
Pressure range (operating pressure)	2.0 - 6.0 bar
Recomm. internal hose diameter compressed air	6 mm
Recomm. internal hose diameter vacuum	12 mm
Weight	190.60 g
Operating temperature	0 ... 60 °C
Pressure range (operating pressure)	29.0 - 87.0
Suction rate (max.)	5.61 cfm
Air consumption suction	3.64 cfm
Product family	SBP-HV-HF-KU

Accessories



SD 29x70 SHC 22

Part no.:10.02.01.01517

External diameter D: 29 mm

Length L: 70 mm

Construction use: Schmalz Holder Cap

Size: 22

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx

Basic Ejector

SBP HV 2 16 22 KU

Part no...:10.02.01.01961

<https://www.schmalz.com/10.02.01.01961>



SD 29x121.5 SHC

Part no...:10.02.01.01831

External diameter D: 29 mm

Length L: 121.5 mm

Construction use: Schmalz Holder Cap

Spare parts



SFE 22 POM

Part no...:10.02.01.01767

Hole diameter: 22 mm

Width B: 31.5 mm

Height H: 45 mm

Length L: 80 mm

Thread G1: G1/4"-F

Thread G2: G3/8"-F

Compressed-air connection: G1/4"-F

Suction cup connection: G3/8"-F



SEP HV 2 16 22

Part no...:10.02.01.01396

Shape: High Vacuum

Number of stages: 2

Nozzle size: 1.6 mm

Hole diameter: 22 mm

Degree of evacuation: 90 %

Pressure range (operating pressure): 2.0 ... 6.0 bar

Pressure optimal: 4 bar

Suction rate (max.): 152.6 l/min

Air consumption suction: 103 l/min

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | +52 442 209 52 26
schmalz@schmalz.com.mx

Basic Ejector

SBP HV 2 16 22 KU

Part no...:10.02.01.01961

<https://www.schmalz.com/10.02.01.01961>



SHC 2 22

Part no...:10.02.01.01512

Number of stages: 2

Hole diameter: 22 mm

External diameter D: 20 mm

Length L: 33 mm

Thread G1: M27x1.5-M

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx