

Bell suction cup (round)

SAG 45 NBR-60 M10-AG

Part no...:10.01.01.12296

<https://www.schmalz.com/10.01.01.12296>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAG > SAG 45 NBR-60 M10-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 45


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Steel

Connection: M10-AG

Design Data



Attribute	Value
dn	4 mm
Dmax(S)	51.50 mm
Ds	47 mm
G1	M10-M
H	36.50 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	7.80 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	68 N
Size	45
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A
Number of folds	0
Weight	27.80 g
Product family	SAG

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | +52 442 209 52 26
schmalz@schmalz.com.mx



Bell suction cup (round)

SAG 45 NBR-60 M10-AG

Part no...:10.01.01.12296

<https://www.schmalz.com/10.01.01.12296>

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx