

Bellows suction cups (round)

SFB1 25 SI-55 G1/8-IG

Part no...:10.01.06.04412

<https://www.schmalz.com/10.01.06.04412>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFB1 25 SI-55 G1/8-IG

Bellows suction cup (round) for very uneven workpieces flexible workpieces




Size: 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Design Data



Attribute	Value
Dmax(S)	26.50 mm
Ds	25 mm
d2	8.20 mm
dn	4.10 mm
G1	G1/8-IG
LG1	8 mm
H	33.20 mm
SW1	14 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	3.20 N
Volume	1.90 cm ³
Size	25
Number of folds	1.50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A
Weight	7.30 g
Product family	SFB1

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269 México | + 52 442 209 5200
schmalz@schmalz.com.mx

Bellows suction cups (round)

SFB1 25 SI-55 G1/8-IG

Part no.:10.01.06.04412

<https://www.schmalz.com/10.01.06.04412>

Spare parts



SFB1 25 SI-55 SC040

Part no.:10.01.06.04370

Size: 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76660 México | + 52 442 209 5200
schmalz@schmalz.com.mx