

Solenoid valve

EMVP 15 24V-DC 3/2 IMP

Part no...:10.05.02.00147

<https://www.schmalz.com/10.05.02.00147>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMVP > EMVP 15 24V-DC 3/2 IMP

Solenoid valve EMVP for vacuum, pneumatic pilot control



Nominal size: 15 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Double pilot valve


Connecting thread: G1/2"-F

Pressure range (operating pressure): bar

Nominal flow rate: 20 m³/h

Weight: 0.55 kg

Design Data



Attribute	Value
B	75 mm
B2	37.50 mm
d	6.50 mm
D	80 mm
G1	G1/2"-F
G2	G1/2"-F
G3	G1/2"-F
G4	G1/8"-F
H	143.60 mm
H1	152.10 mm
H2	22.50 mm
L	75 mm
L1	111.50 mm
X1	63 mm
Y1	32.50 mm

Technical Data

Attribute	Value
Nominal size	15 mm
Nominal flow rate	20 m ³ /h

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 66
schmalz@schmalz.com.mx

Solenoid valve

EMVP 15 24V-DC 3/2 IMP

Part no...:10.05.02.00147

<https://www.schmalz.com/10.05.02.00147>

Control valve	Double pilot valve
Nominal flow rate	333 l/min
Power consumption DC	5 W
Voltage DC	24V - DC
Closing time	110 ms
Weight	0.55 kg
Product family	EMVP

Accessories




FAS 80x33.8 G1/2-AG

Part no...:10.05.01.00061

External diameter D: 80 mm

Length L: 33.8 mm

Thread G1: G1/2"-M



ASK B-Form-C 5000 K-3P

Part no...:21.04.06.00084

Electrical connection: Fem connect Form C

Cable length: 5,000 mm

Material hose: PVC cable

Contact Schmalz

Schmalz S. de R.L. de C.V. | 1er. retorno universitario # 1 Interior 2 A, Terra Business Park, Col. La Pradera, El Marqués, Querétaro, C.P. 76269, México | + 52 442 209 52 26
schmalz@schmalz.com.mx