

## Flat suction cup (round)

SUF 25 SI-CO-55 G1/8-IG

Part no.:10.01.01.14144

<https://www.schmalz.com/10.01.01.14144>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 25 SI-CO-55 G1/8-IG

### Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces



Size: 25

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Vacuum connection: G1/8"-F

### Design Data



| Attribute  | Value    |
|------------|----------|
| Dmax(S)    | 28.20 mm |
| Ds         | 25 mm    |
| dn         | 4.10 mm  |
| G1         | G1/8"-F  |
| H          | 25.20 mm |
| LG1        | 8 mm     |
| SW1        | 14 mm    |
| Z (Stroke) | 2.50 mm  |

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction force (-600mbar)    | 23 N                   |
| Pull-off force              | 23 N                   |
| Volume                      | 0.90 cm <sup>3</sup>   |
| Curve radius (min) (convex) | 25 mm                  |
| Hose diameter (rec.) d      | 4 mm                   |
| Size                        | 25                     |
| Suction cup material        | Silicone SI conductive |
| Material hardness [Shore A] | 55 Shore A             |

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Flat suction cup (round)

SUF 25 SI-CO-55 G1/8-IG

Part no.:10.01.01.14144

<https://www.schmalz.com/10.01.01.14144>

|                 |         |
|-----------------|---------|
| Weight          | 10.50 g |
| Product family  | SUF     |
| Number of folds | 0       |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Spare parts



#### SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm



#### SUF 25 SI-CO-55 SC040

Part no.:10.01.01.14039

Size: 25

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)