

Suction plate (oval)


SPLO 300x30 NBR-55

Part no.:10.01.05.00184

<https://www.schmalz.com/10.01.05.00184>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Suction Plates SPLO > SPLO 300x30 NBR-55

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 300 x 30

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Height H: 20 mm

Design Data



Attribute	Value
Bk	30 mm
Bmax(S)	33 mm
Bs	30 mm
H	20 mm
H2	6 mm
Lk	320 mm
Lmax(S)	304 mm
Ls	300 mm
Z (Stroke)	5 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	400 N
Volume	32.43 cm ³
Curve radius (min) (convex)	30 mm
Number of folds	0
Dimensions (LxB)	300 x 30
Suction cup material	Nitrile rubber NBR
Weight	600 g

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Suction plate (oval)

SPLO 300x30 NBR-55

Part no...:10.01.05.00184

<https://www.schmalz.com/10.01.05.00184>

Product family

SPLO

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
