

Bellows suction cups (round)

FSGA 40 VU1-72 G1/4-IG ON

Part no.:10.01.06.00299

<https://www.schmalz.com/10.01.06.00299>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bellows Suction Cups FSGA VU1 (1.5 Folds) > FSGA 40 VU1-72 G1/4-IG ON

Bellows suction cup (round) with optimal adaptation to uneven surfaces



Size: 40

Suction cup material: Vulkollan VU1


Material hardness [Shore A]: 72 Shore A

Nipple material: Aluminum

Connection: G1/4"-F

Number of folds: 1.5

Design Data



Attribute	Value
d2	26.80 mm
dn	3.50 mm
Dmax(S)	42.50 mm
Ds	38 mm
G1	G1/4"-F
H	41 mm
LG1	12 mm
SW1	17 mm
Z (Stroke)	12.80 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	33 N
Pull-off force	56 N
Volume	11.30 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	6 mm
Size	40
Nipple family	N 011

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bellows suction cups (round)

FSGA 40 VU1-72 G1/4-IG ON

Part no.:10.01.06.00299

<https://www.schmalz.com/10.01.06.00299>

Suction cup material	Vulkollan VU1
Material hardness [Shore A]	72 Shore A
Weight	16.10 g
Product family	FSGA
Number of folds	1.50

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N011 G1/4-IG DN350

Part no.:10.01.01.00412

Nipple family: N 011
Thread G1: G1/4"-F
Length L1: 24.5 mm
Length L: 15 mm
Fitting length: 15 mm
Nominal diameter dn: 3.5 mm
Material: Aluminum
Spanner size SW2: 5 mm



FGA 40 VU1-72 N011 ON

Part no.:10.01.06.00301

Size: 40
Suction cup material: Vulkollan VU1
Material hardness [Shore A]: 72 Shore A
Number of folds: 1.5

Bellows suction cups (round)

FSGA 40 VU1-72 G1/4-IG ON

Part no...:10.01.06.00299

<https://www.schmalz.com/10.01.06.00299>



FGA 40 VU1-72 N011 ON

Part no...:10.01.06.00301

Size: 40

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Number of folds: 1.5