

Bellows suction cup (round)

FGA 110 NBR-55 N010

Part no.:10.01.06.00629

<https://www.schmalz.com/10.01.06.00629>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 110 NBR-55 N010

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 110

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	7 mm
d2	80 mm
D1	123 mm
Dk	86 mm
Dmax(S)	130 mm
Dmk	40 mm
Ds	111 mm
H	55 mm
H4	8 mm
Z (Stroke)	29 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1.50
Size	110
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Product family	FGA

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bellows suction cup (round)

FGA 110 NBR-55 N010

Part no.:10.01.06.00629

<https://www.schmalz.com/10.01.06.00629>

Accessories



SA-NIP N010 G1/2-IG

Part no.:10.01.01.00796

Thread G1: G1/2"-F

Material: Aluminum