

Bellows suction cup (round)

FG 3 NBR-55 N055

Part no.:10.01.06.03704

<https://www.schmalz.com/10.01.06.03704>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 3 NBR-55 N055

Bellows suction cup (round) for very uneven workpieces




Size: 3

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2.5

Design Data



Attribute	Value
d	1.70 mm
d1	2.30 mm
d2	1.80 mm
D1	3.60 mm
Dk	3.60 mm
Dmax(S)	4 mm
Ds	3 mm
H	6.70 mm
H2	2.10 mm
H3	2.70 mm
Z (Stroke)	1.10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	0.15 N
Pull-off force	0.40 N
Volume	0.02 cm ³
Curve radius (min) (convex)	4 mm
Hose diameter (rec.) d	2 mm
Size	3

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bellows suction cup (round)

FG 3 NBR-55 N055

Part no...:10.01.06.03704

<https://www.schmalz.com/10.01.06.03704>

Nipple family	N 055
Number of folds	2.50
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Product family	FG