

## Bellows suction cup f SCG(S)-gripper


BCG 50 SI-MD-55 SC095

Part no...:10.01.06.04561

<https://www.schmalz.com/10.01.06.04561>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > BCG 50 SI-MD-55 SC095

### Bellows suction cup (round) for high volumeflow with optimum adaption to uneven surfaces




Size: 50

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d2         | 33 mm    |
| Dmax(S)    | 52 mm    |
| Ds         | 49.40 mm |
| H          | 22 mm    |
| Z (Stroke) | 8 mm     |

### Technical Data

| Attribute                   | Value                        |
|-----------------------------|------------------------------|
| Suction cup material        | Silicone SI metal detectable |
| Material hardness [Shore A] | 55 Shore A                   |
| Weight                      | 11 g                         |

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)