

## Bellows suction cup f SCG(S)-gripper

BCG 40 NBR-ESD-55 SC095

Part no...:10.01.06.04575

<https://www.schmalz.com/10.01.06.04575>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > BCG 40 NBR-ESD-55 SC095

### Bellows suction cup (round) for high volumeflow with optimum adaption to uneven surfaces




Size: 40

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d2         | 26 mm    |
| Dmax(S)    | 42 mm    |
| Ds         | 39.40 mm |
| H          | 19.50 mm |
| Z (Stroke) | 6.50 mm  |

### Technical Data

| Attribute                   | Value                  |
|-----------------------------|------------------------|
| Suction cup material        | Nitrile rubber NBR-ESD |
| Material hardness [Shore A] | 55 Shore A             |
| Weight                      | 8 g                    |

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)