

Sealing magnet

ISMST 19-7 4ISMST

Part no...:10.01.14.00847

<https://www.schmalz.com/10.01.14.00847>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISMST 19-7 4ISMST


Sealing magnet for clamping system Innospann



External diameter D: 7 mm

Height H: 11.5 mm

Design Data



Attribute	Value
D	7 mm
Dk	19 mm
H	11.50 mm

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl