

Quad-Base

ISQB-R 175x175x15 30/50

Part no...:10.01.15.00183

<https://www.schmalz.com/10.01.15.00183>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISQB-R 175x175x15 30/50

Quad-Base for grid tables



Dimensions (LxB): 175x175


Basic area: 175 x 175 mm

Length L: 175 mm

Width B: 175 mm

Height H: 15 mm

Design Data



Attribute	Value
B	175 mm
d	60 mm
H	15 mm
L	175 mm

Technical Data

Attribute	Value
Weight	0.93 kg

Accessories

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Quad-Base

ISQB-R 175x175x15 30/50

Part no...:10.01.15.00183

<https://www.schmalz.com/10.01.15.00183>



ISCUP Cup 1 80x80x30

Part no...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Part no...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm



ISCUP Cup 3 80x28x30

Part no...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl