

Mono-Base

ISMB 80x80x26

Part no...:10.01.15.00214

<https://www.schmalz.com/10.01.15.00214>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Innospann Clamping Equipment ISCUP/ISMB/ISQB > ISMB 80x80x26

Mono-Base for Steelplate and Adapterplate




Basic area: 80 x 80 mm

Length L: 80 mm

Width B: 80 mm

Height H: 26 mm

Design Data



Attribute	Value
B	80 mm
H	26 mm
L	80 mm

Technical Data

Attribute	Value
Weight	0.07 kg

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl