

Friction plate


ISRPL 66x66x8.5 NK-45 d12

Part no...:10.01.15.00343

<https://www.schmalz.com/10.01.15.00343>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 66x66x8.5 NK-45 d12

Friction plate



Width B: 66 mm

Internal diameter d: 12 mm


Height H: 8.5 mm

Length L: 66 mm

Suction cup material: Natural rubber NK-45

Type: Cup 1

Design Data



Attribute	Value
B	66 mm
d	12 mm
H	8.50 mm
L	66 mm

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl