

Friction plate


ISRPL 66x26x8.5 NK-45 d12

Part no...:10.01.15.00344

<https://www.schmalz.com/10.01.15.00344>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 66x26x8.5 NK-45 d12

Friction plate



Width B: 26 mm

Internal diameter d: 12 mm


Height H: 8.5 mm

Length L: 66 mm

Suction cup material: Natural rubber NK-45

Type: Cup 2

Design Data



Attribute	Value
B	26 mm
d	12 mm
H	8.50 mm
L	66 mm