

Friction ring

REIB-RING SGM 30 PU-55

Part no.:10.01.17.00385

<https://www.schmalz.com/10.01.17.00385>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > REIB-RING SGM 30 PU-55

Friction ring




Construction use: Magnetic gripper

Size: 30

External diameter D: 29.5 mm

Internal diameter d: 20.5 mm

Design Data



Attribute	Value
D	29.50 mm
L	10.70 mm

Technical Data

Attribute	Value
Size	30
Suction cup material	Polyurethane PU
Operating temperature (max.)	100 °C
Material hardness [Shore A]	55 Shore A
Weight	3 g

Material HT2: Operating temperature max. short-term up to +250 °C

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl