

Quick change suction cup

SQC-C-RU-80x62-NBR

Part no...:10.01.18.01033

<https://www.schmalz.com/10.01.18.01033>

Home > Vacuum Clamping Technology > Clamping Equipment for Glass Processing > Quick-Change Systems for Bystronic Machines > Schmalz Quick-Change SQC > SQC-C-RU-80x62-NBR

Quick Change Suction Cup



External diameter D: 80 mm

Height H: 62 mm

Construction use: Quick-change system

Dimensions (LxB): Diameter 80 mm


Material: Aluminum

Material: ED

Material hardness [Shore A]: 85 Shore A

Sealing material: Perbunan

Design Data



Attribute	Value
D	80 mm
H	62 mm
H1	79.80 mm

Spare parts

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Quick change suction cup

SQC-C-RU-80x62-NBR

Part no...:10.01.18.01033

<https://www.schmalz.com/10.01.18.01033>



V-RING 63x11 V-070 NBR

Part no...:10.07.08.00554

External diameter D: 75 mm

Type: V-070