

Suction cup (round)


SAUG-SCGS 40 SI-MD-55 602 B

Part no...:10.01.30.01089

<https://www.schmalz.com/10.01.30.01089>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 40 SI-MD-55 602 B

Suction cup (round)




Size: 40

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A

Suct. cups: Bell. suct. cup f. SCG(S)

Design Data



Attribute	Value
Dmax (N)	25 mm
Dmax(S)	42 mm
dn	27 mm
Ds	39.40 mm
G1	M20x1-F
H	29 mm
LG1	6.50 mm
Z (Stroke)	6.50 mm

Technical Data

Attribute	Value
Size	40
Suction cup material	Silicone SI metal detectable
Material hardness [Shore A]	55 Shore A
Weight	26 g
Product family	SAUG-SCGS

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl


Suction cup (round)

SAUG-SCGS 40 SI-MD-55 602 B

Part no.:10.01.30.01089

<https://www.schmalz.com/10.01.30.01089>

Spare parts



BCG 40 SI-MD-55 SC095

Part no.:10.01.06.04560

Size: 40

Suction cup material: Silicone SI metal detectable

Material hardness [Shore A]: 55 Shore A