

Exhaust air set

ABL-SET SBPL/SCPL L

Part no.:10.02.01.01940

<https://www.schmalz.com/10.02.01.01940>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Basic Ejectors > ABL-SET SBPL/SCPL L

Exhaust air set




Size: L

Length L: 71 mm

Width B: 31 mm

Height H: 97 mm

Design Data



Attribute	Value
B	31 mm
B1	40.50 mm
d1	4.50 mm
G4	G1"-F
H	97 mm
L	71 mm
X1	60 mm
Y1	20 mm

Technical Data

Attribute	Value
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	62 g

Accessories

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Exhaust air set

ABL-SET SBPL/SCPL L

Part no...:10.02.01.01940

<https://www.schmalz.com/10.02.01.01940>



ST G1/2-AG 19 MS-V

Part no...:10.08.03.00163

Thread G1: G1/2"-M

Hose diameter (rec.) d: 19 mm

Material: Brass

Surface: nickel plated

Length L: 10 mm

Nominal diameter dn: 14.3 mm



ST G1-AG 32 MS-V

Part no...:10.08.03.00168

Thread G1: G1"-M

Hose diameter (rec.) d: 32 mm

Material: Brass

Surface: nickel plated

Length L: 10.5 mm

Nominal diameter dn: 26 mm



VSL 26-19 PVC-DS KL-TR

Part no...:10.07.09.00007

External diameter D: 26 mm

Internal diameter d: 19 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz


Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Exhaust air set

ABL-SET SBPL/SCPL L

Part no...:10.02.01.01940

<https://www.schmalz.com/10.02.01.01940>



VSL 41-32 PVC-DS KL-TR

Part no...:10.07.09.00008

External diameter D: 41 mm

Internal diameter d: 32 mm


Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C



SSB 20-32 ST-VZ

Part no...:10.07.10.00003

Clamping range: 20.0 ... 32.0 mm

Material: Steel

Surface: galvanised



SSB 32-50 ST-VZ

Part no...:10.07.10.00004

Clamping range: 32.0 ... 50.0 mm

Material: Steel

Surface: galvanised