

CobotPump
ECBPMi-RS-485 24V-DC FK

Part no...:10.03.01.00584

<https://www.schmalz.com/10.03.01.00584>




Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Generators End-of-Arm > ECBPMi-RS-485 24V-DC FK

CobotPump (Mini) for electrical vacuum generation for collaborative robots



Voltage DC: 24V - DC
Rated current: 0.3 A
Electrical connection: Spring contact
Inputs/outputs: RS 485
Operating temperature: 0 ... 40 °C
Suction rate (max.): 1.6 l/min
Rated power: 7.2 W

Design Data



Attribute	Value
D	63 mm
D2	35.50 mm
D mk1	46 mm
G1	M4-F
G2	G1/4"-F
L	56.40 mm
L1	61.40 mm
LG1	6 mm
LG2	11 mm

Technical Data

Attribute	Value
Suction rate (max.)	1.60 l/min
Voltage DC	24V - DC
Rated power	7.20 W
Rated current	0.30 A
Electrical connection	Spring contact
Operating temperature	0 ... 40 °C