

Vacuum blower

SB 440 360 6.6 IE3-TYP2 ER

Part no...:10.04.01.00145

<https://www.schmalz.com/10.04.01.00145>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB with Electro-Pneumatic Reversing > SB 440 360 6.6 IE3-TYP2 ER

Vacuum Blower for high suction rate



Suction rate (60 Hz): 440 m³/h

Vacuum (60 Hz): 360 mbar

Rated power 60 Hz: 6.6 kW

Construction: IE3:US/CAN


Voltage at 60Hz: YY230/Y460V ±10%

Permission: UL/CSA

with: Electro-pneumatic reversing

Weight: 110.5 kg

Design Data



Attribute	Value
B	537 mm
B1	559 mm
d	13 mm
G1	G2-1/2"-M
H	646 mm
H2	134 mm
L	1146 mm
X1	730 mm
Y1	506 mm

Technical Data

Attribute	Value
Max. vacuum	360 mbar
Protection type IP	IP 55
Weight	110.50 kg
Voltage at 60Hz	YY230/Y460V ±10%
Permission	UL/CSA
Product family	SB-ER

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl



Vacuum blower

SB 440 360 6.6 IE3-TYP2 ER

Part no...:10.04.01.00145

<https://www.schmalz.com/10.04.01.00145>

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl