

Vacuum blower

SB 325 265 3 IE3-TYP3 ER

Part no...:10.04.01.00149

<https://www.schmalz.com/10.04.01.00149>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Blowers > Vacuum Blowers SB with Electro-Pneumatic Reversing > SB 325 265 3 IE3-TYP3 ER

Vacuum Blower for high suction rate



Suction rate (50 Hz): 325 m³/h

Suction rate (60 Hz): 390 m³/h

Vacuum (50 Hz): 265 mbar

Vacuum (60 Hz): 245 mbar

Rated power 50 Hz: 3 kW

Rated power 60 Hz: 3.6 kW

Construction: IE3:JPN/KOR/BRA


Voltage at 50Hz: D200V/Y350V ±10 %

Voltage at 60Hz: D220V/Y380-400V ±10%

with: Electro-pneumatic reversing

Weight: 78 kg

Design Data



Attribute	Value
B	439 mm
B1	502 mm
d	13 mm
G1	G2"-M
H	476 mm
H2	134 mm
L	798 mm
X1	435 mm
Y1	446 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	325 m ³ /h
Max. vacuum	265 mbar
Rated power 50 Hz	3 kW
Protection type IP	IP 55
Weight	78 kg
Voltage at 50Hz	D200V/Y350V ±10 %

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl



Vacuum blower

SB 325 265 3 IE3-TYP3 ER

Part no...:10.04.01.00149

<https://www.schmalz.com/10.04.01.00149>

Voltage at 60Hz

D220V/Y380-400V $\pm 10\%$

Product family

SB-ER

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl