

Solenoid valve pressure

EMV 2.5 24V-DC 3/2 NC K-2P

Part no.:10.05.01.00289

<https://www.schmalz.com/10.05.01.00289>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Thin Glass Grippers > Accessories STGG > EMV 2.5 24V-DC 3/2 NC K-2P

Solenoid valve EMV for direct control of compressed air



Nominal size: 2.5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally closed

Connecting thread: G1/8"-M

Pressure range (operating pressure): 3.5 ... 7.0 bar

Interface electrical connection: Cable, 2 pol

Design Data



Attribute	Value
B1	31.70 mm
B2	10.70 mm
d	4 mm
G1	G1/8"-M
G2	M5-F
L	51.70 mm
L1	56.50 mm

Technical Data

Attribute	Value
Nominal size	2.50 mm
Control valve	Normally closed
Nominal flow rate	135 l/min
Nominal flow rate	8.10 m³/h
Voltage DC	24V - DC
Weight	0.10 kg
Product family	EMV

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl



Solenoid valve pressure

EMV 2.5 24V-DC 3/2 NC K-2P

Part no...:10.05.01.00289

<https://www.schmalz.com/10.05.01.00289>

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl