

Solenoid valve

EMV 2 24V-DC 3/2 NC

Part no.:10.05.01.00290

<https://www.schmalz.com/10.05.01.00290>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMV > EMV 2 24V-DC 3/2 NC

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 2 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally closed

Connecting thread: G1/8"-F

Pressure range (operating pressure): bar

Power consumption DC: 2.2 W

Design Data



Attribute	Value
B	25 mm
G1	G1/8"-F
G2	G1/8"-F
G5	M5-F
H	70 mm
L	68 mm
X1	30 mm
Y1	16 mm

Technical Data

Attribute	Value
Nominal size	2 mm
Control valve	Normally closed
Nominal flow rate	16.70 l/min
Nominal flow rate	1 m ³ /h
Power consumption DC	2.20 W
Voltage DC	24V - DC
Closing time	10 ms
Weight	0.15 kg

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl



Solenoid valve

EMV 2 24V-DC 3/2 NC

Part no...:10.05.01.00290

<https://www.schmalz.com/10.05.01.00290>

Product family

EMV

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl