

## Flat suction cup (round)

SUF 25 NBR-55 SC040

Part no.:10.01.01.13948

<https://www.schmalz.com/10.01.01.13948>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 25 NBR-55 SC040

### Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

### Design Data



| Attribute  | Value    |
|------------|----------|
| d1         | 10.50 mm |
| d          | 7 mm     |
| Dk         | 15.50 mm |
| Dmax(S)    | 28.20 mm |
| Ds         | 25 mm    |
| H          | 11.20 mm |
| H2         | 4.80 mm  |
| H3         | 6.70 mm  |
| Z (Stroke) | 2.50 mm  |

### Technical Data

| Attribute                   | Value                |
|-----------------------------|----------------------|
| Suction force (-600mbar)    | 23 N                 |
| Pull-off force              | 23 N                 |
| Volume                      | 0.90 cm <sup>3</sup> |
| Curve radius (min) (convex) | 25 mm                |
| Size                        | 25                   |
| Nipple family               | SC040                |
| Suction cup material        | Nitrile rubber NBR   |
| Material hardness [Shore A] | 55 Shore A           |
| Weight                      | 2.50 g               |

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)

## Flat suction cup (round)

SUF 25 NBR-55 SC040

Part no.:10.01.01.13948

<https://www.schmalz.com/10.01.01.13948>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

### Accessories



#### SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



#### SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

### Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | [info@schmalz.nl](mailto:info@schmalz.nl)