

Bellows suction cup (round)

SPB1 30 ED-65 SC040

Part no...:10.01.06.02454

<https://www.schmalz.com/10.01.06.02454>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPB1 30 ED-65 SC040

Bellows suction cup (round) with 1.5 corr. for dynamic handling of cardboard and rigid packaging




Size: 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	7.50 mm
d1	10.50 mm
d2	20 mm
D1	34.20 mm
Dk	15.10 mm
Dmax(S)	36.70 mm
Ds	31.40 mm
H	23 mm
H2	4.60 mm
Z (Stroke)	13 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	20.70 N
Pull-off force	30.60 N
Lateral force	15.50 N
Volume	7.99 cm ³
Curve radius (min) (convex)	25 mm
Hose diameter (rec.) d	6 mm
Size	30

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bellows suction cup (round)

SPB1 30 ED-65 SC040

Part no.:10.01.06.02454

<https://www.schmalz.com/10.01.06.02454>

Nipple family	SC 040
Number of folds	1.50
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	3.70 g
Product family	SPB1

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 040 G1/8-AG

Part no.:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20.2 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Bellows suction cup (round)

SPB1 30 ED-65 SC040

Part no...:10.01.06.02454

<https://www.schmalz.com/10.01.06.02454>



SIEB 11x1 MS-A2 280 0.28/0.16

Part no...:10.07.01.00309

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SPI 26 PA SPB1-30

Part no...:10.01.06.03386

Size: 26

Material: Polyamide

Use: SPB1-30



SC 040 NPT1/8-AG

Part no...:10.01.06.02541

Connection geometry: 040

Connection: NPT1/8-M

Length L1: 20.9 mm

Fitting length: 6 mm

Nominal diameter dn: 4.1 mm

Bellows suction cup (round)

SPB1 30 ED-65 SC040

Part no...:10.01.06.02454

<https://www.schmalz.com/10.01.06.02454>



SC 040 NPT1/8-IG

Part no...:10.01.06.02542

Connection geometry: 040

Connection: NPT1/8-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm