

Friction plate

ISRPL 66x14x8.5

Part no...:10.01.15.00019

<https://www.schmalz.com/10.01.15.00019>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Flexibilization of CNC Machining Centers > Accessories and Spare Parts > ISRPL 66x14x8.5

Friction plate




Width B: 14 mm

Height H: 8.5 mm

Length L: 66 mm

Type: Cup 3

Design Data



Attribute	Value
B	14 mm
H	8.50 mm
L	66 mm

Spare parts

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Friction plate

ISRPL 66x14x8.5

Part no.:10.01.15.00019

<https://www.schmalz.com/10.01.15.00019>



SIEB 11x1 MS-A2 100

Part no.:10.07.01.00085

External diameter D: 11 mm

Length L: 1 mm

Material: MS-A2

Filter pore size: 100 µm

Material: Brass / Stainless steel