

Sealing profile (meter)

DI-PROF 4x6 MOS NK-20 HR

Part no.:10.07.04.00054

<https://www.schmalz.com/10.07.04.00054>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 4x6 MOS NK-20 HR

Sealing section for construction of specific gripper solutions



Width B: 4 mm

Height H: 6 mm


Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Form: half-round

Design Data



Attribute	Value
B	4 mm
H	6 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Natural Rubber NK
Weight	20 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl