

Suction Cup Balance SSCB

SSCB-30 60.7-66.5 ZP M4-IG SAB-NBR

Part no.:10.01.41.00017

<https://www.schmalz.com/10.01.41.00017>

Home > Vacuum Clamping Technology > Clamping Equipment for 3D Freeform Surfaces > Clamping and Gripping Equipment for Automated Processing > Suction Cup Balance SSCB > SSCB-30 60.7-66.5 ZP M4-IG SAB-NBR

Vacuum Clamping System for automated 3D-fixation



Pitch diameter D mk: 30 mm

Function Suction cup: Centrally fixed pins

Suct. cups: Bellows suct. cup SAB

Connection: M4-IG


Material: NBR

Material hardness [Shore A]: 60 Shore A

Material: NBR

Height H1: 71.8 mm

Design Data



Attribute	Value
D1	66 mm
Dmk	30 mm
G1	M4-F
G2	M3-M
H1	71.80 mm
EH (min)	60.70 mm
EH (max)	66.50 mm
Zs	5.80 mm
Z (Stroke)	8 mm

Technical Data

Attribute	Value
Size	22
Weight	200 g
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl