

Vacuum block

VCBL-R 160x96x125 30/50 TV

Part no.:10.01.12.03422

<https://www.schmalz.com/10.01.12.03422>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block
VCBL-R > VCBL-R 160x96x125 30/50 TV

Vacuum block for grid tables



Length L: 160 mm

Width B: 96 mm


Height H: 125 mm

Grid: 30/50

Recommended slot width x slot depth [mm]: 6,5x6,5 / 7,5x7,5 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	96 mm
H	125 mm
H2	102 mm
L	160 mm
L1	160 mm

Technical Data

Attribute	Value
Grid	30/50

Spare parts

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuum block

VCBL-R 160x96x125 30/50 TV

Part no...:10.01.12.03422

<https://www.schmalz.com/10.01.12.03422>



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



ERS VCBL-R Winkel

Part no...:10.01.12.02691



ERS VCBL-R


Part no...:10.01.12.02693

Vacuum block

VCBL-R 160x96x125 30/50 TV

Part no...:10.01.12.03422

<https://www.schmalz.com/10.01.12.03422>



ISDR 150x150x13.5 R 30/50

Part no...:10.01.15.00352

Length L: 150 mm

Width B: 150 mm

Height H: 13.5 mm

Type: R 30/50