

Vacuum/pressure switch pneumatic

VS-V-PM-NO

Part no.:10.06.02.00456

<https://www.schmalz.com/10.06.02.00456>

Home > Vacuum Technology for Automation > Vacuum Components > Switches and System Monitoring > Mechanic Vacuum Switches > Vacuum Switches VS-V-PM/EM-ST > VS-V-PM-NO

Vacuum switch, pneumatic, with pneumatic output signal




Measuring range: -1,0 ... 0,0 bar

Construction shape vacuum switch: Normally open

Hysteresis: Fixed: approx. 10 mbar

Design Data



Attribute	Value
B	19.80 mm
d	4 mm
d3	4.20 mm
G2	M5-F
H	40 mm
L	58 mm
X1	41 mm

Technical Data

Attribute	Value
Overpressure resistance	6 bar
Repeatability	± 3% of full-scale value
Hysteresis	Fixed: approx. 10 mbar
Construction shape vacuum switch	Normally open
Weight	33 g
Product family	VS-V-PM / EM-ST

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl