

Vacuum pump

EVE-WR 25 AC3

Part no.:10.03.05.00014

<https://www.schmalz.com/10.03.05.00014>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Vacuum Pumps > Water-Ring Pumps EVE-WR > EVE-WR 25 AC3

Water-ring pump, wear-free, robust, requires little maintenance



Suction rate (50 Hz): 25 m³/h

Current type: three-phase current

Sound level at 50 Hz: 63 dB(A)


Voltage at 50Hz: 200-240V or 345-420V

Rated power 50 Hz: 0.83 kW

Rated power 60 Hz: 0.83 kW

Weight: 38 kg

Design Data



Attribute	Value
B	432 mm
d	14 mm
D2	30 mm
H	390 mm
H1	486 mm
L	602 mm
L2	85 mm
X1	345 mm
Y1	370 mm

Technical Data

Attribute	Value
Suction rate (50 Hz)	25 m ³ /h
Voltage at 50Hz	200-240V or 345-420V
Voltage at 60Hz	200-275V o. 345-480V
Rated power 50 Hz	0.83 kW
Rated power 60 Hz	0.83 kW
Sound level at 50 Hz	63 dB(A)
Weight	38 kg
Protection type IP	IP 54

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Vacuum pump

EVE-WR 25 AC3

Part no.:10.03.05.00014

<https://www.schmalz.com/10.03.05.00014>

Current type

AC3

Accessories



MSS-K 2.5-4A

Part no.:10.04.04.00120

Construction use: PKZM0

Protection type IP: IP 65

Measuring range: bar

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 |
info@schmalz.nl