

Flat suction cup (round)

PFG 20 NBR-ESD-55 N006

Part no.:10.01.01.13786

<https://www.schmalz.com/10.01.01.13786>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 20 NBR-ESD-55 N006

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 20

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	4.50 mm
d1	11 mm
Dk	15.20 mm
Dmax(S)	23 mm
Ds	20 mm
H	10 mm
H2	4.50 mm
Z (Stroke)	2.20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	15.50 N
Volume	0.86 cm ³
Curve radius (min) (convex)	20 mm
Size	20
Nipple family	N 006
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

PFG 20 NBR-ESD-55 N006

Part no.:10.01.01.13786

<https://www.schmalz.com/10.01.01.13786>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N006 G1/8-AG DN200

Part no.:10.01.01.03530

Thread G1: G1/8"-M

Length L1: 19.5 mm

Fitting length: 5 mm

Material: Aluminum



SA-NIP N006 G1/8-IG DN200

Part no.:10.01.01.03522

Thread G1: G1/8"-F

Length L1: 22.5 mm

Fitting length: 16 mm

Material: Aluminum

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl