

Flat suction cup (round)

SUF 4 SI-CO-55 SC010

Part no.:10.01.01.14021

<https://www.schmalz.com/10.01.01.14021>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 4 SI-CO-55 SC010

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 4

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	1.40 mm
Dk	4.20 mm
Dmax(S)	4.70 mm
Ds	4 mm
H	3.50 mm
H2	2 mm
Z (Stroke)	0.40 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	0.40 N
Pull-off force	0.40 N
Volume	0.01 cm ³
Curve radius (min) (convex)	8 mm
Size	4
Nipple family	SC010
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A
Weight	0 g

Contact Schmalz

Schmalz B.V. | Generatorstraat 34, 7556 RC Hengelo, Netherlands | +31 74 255 5757 | info@schmalz.nl

Flat suction cup (round)

SUF 4 SI-CO-55 SC010

Part no...:10.01.01.14021

<https://www.schmalz.com/10.01.01.14021>

Product family

SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SC 010 M3-AG

Part no...:10.01.06.04249

Connection geometry: 010

Vacuum connection: M3-M

Fitting length: 2 mm

Nominal diameter dn: 1 mm