

## Bell suction cup (round)

SAX 60 ED-85 G3/8-IG

Part no...:10.01.19.00152

<https://www.schmalz.com/10.01.19.00152>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAX > SAX 60 ED-85 G3/8-IG

### Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 60


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Connection: G3/8"-F

Number of folds: 0

### Design Data



| Attribute  | Value    |
|------------|----------|
| dn         | 6.75 mm  |
| Dmax(S)    | 69.70 mm |
| Ds         | 61.50 mm |
| G1         | G3/8"-F  |
| H          | 33.40 mm |
| LG1        | 12 mm    |
| SW1        | 22 mm    |
| Z (Stroke) | 10.90 mm |

### Technical Data

| Attribute                    | Value                 |
|------------------------------|-----------------------|
| Suction force (-600mbar)     | 154 N                 |
| Lateral force                | 107 N                 |
| Lateral force (oily surface) | 155 N                 |
| Volume                       | 25.20 cm <sup>3</sup> |
| Curve radius (min) (convex)  | 30 mm                 |
| Size                         | 60                    |
| Connection                   | G3/8"-F               |
| Number of folds              | 0                     |

### Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | [schmalz@schmalz.pl](mailto:schmalz@schmalz.pl)

## Bell suction cup (round)

SAX 60 ED-85 G3/8-IG

Part no.:10.01.19.00152

<https://www.schmalz.com/10.01.19.00152>

|                             |              |
|-----------------------------|--------------|
| Suction cup material        | Elastodur ED |
| Material hardness [Shore A] | 85 Shore A   |
| Weight                      | 29.50 g      |
| Product family              | SAX          |

### Product recommendations



#### HT-SG A3 I 10 31 G3/8-AG AB

Part no.:10.07.06.00356

Connection 1: Ball head 28.5 mm

Shape: integrated nozzle

Suction cup connection: G3/8"-M

Vacuum connection: G1/8"-F

Add. function: Active blowing off



#### FSTE-HDB G3/8-AG 25 VG-AB

Part no.:10.01.02.01436

Suction cup connection: G3/8"-M

Vacuum connection: G1/8"-F

Spring stroke Z: 25 mm

Shape mounting elements: with anti-rotation guard anti-block

### Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | [schmalz@schmalz.pl](mailto:schmalz@schmalz.pl)

## Bell suction cup (round)

SAX 60 ED-85 G3/8-IG

Part no...:10.01.19.00152

<https://www.schmalz.com/10.01.19.00152>



### SAB 60 NBR-60 G3/8-IG

Part no...:10.01.06.00674

Size: 60

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G3/8-IG

Number of folds: 1.5