

Sealing profile (meter)

DI-PROF 30x25 2K-SWG NK-20/55

Part no.:10.07.04.00041

<https://www.schmalz.com/10.07.04.00041>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Sealing Profiles > Sealing Profiles DI-PROF > DI-PROF 30x25 2K-SWG NK-20/55

Sealing section for construction of specific gripper solutions



Width B: 30 mm


Height H: 25 mm

Material type: 2 Comp. sponge rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Design Data



Attribute	Value
B	30 mm
B1	32 mm
B2	2 mm
B3	24 mm
H	25 mm
H1	53 mm
H2	8 mm
H3	10 mm
H4	17 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 E3

Technical Data

Attribute	Value
Sealing material	Natural Rubber NK
Weight	1,201.20 g
Material hardness [Shore A]	20 Shore A
Product family	DI-PROF

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl