

Plug union, straight

STV-GE G3/8-AG 12

Part no.:10.08.02.00209

<https://www.schmalz.com/10.08.02.00209>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-GE G3/8-AG 12

Push-in Fitting, straight



Thread G1: G3/8"-M

Hose diameter: 12 mm


Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 19.5 mm

Length L: 23.6 mm

Design Data



Attribute	Value
D	19.50 mm
d	12 mm
G1	G3/8"-M
dn	9 mm
L	23.60 mm
L1	31 mm
L2	17.60 mm
LG1	7.40 mm
SW1	20 mm

Technical Data

Attribute	Value
Hose type	Hose D = 12 d = 9
Hose type	12-9
Material	Brass
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	35 g
Product family	STV

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Plug union, straight

STV-GE G3/8-AG 12

Part no.:10.08.02.00209

<https://www.schmalz.com/10.08.02.00209>

Accessories



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C