

Holder system

HTS-A3 SGM-HP 50 OP

Part no...:10.01.17.00562

<https://www.schmalz.com/10.01.17.00562>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Holder System Magnetic Grippers
SGM-HP/-HT > HTS-A3 SGM-HP 50 OP

Holder system




Connection 1: Ball head 28.5 mm

Construction use: Magnetic gripper SGM-HP

Size: 50

Design Data



Attribute	Value
B	29 mm
d	4.50 mm
D	28.50 mm
H	9.40 mm
H1	48.30 mm
H2	6 mm
H3	27.10 mm
H4	35 mm
L	110 mm
X1	100 mm
Y1	15 mm

Technical Data

Attribute	Value
Size	50
Material	Aluminum
Weight	107 g
Size	50

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Holder system

HTS-A3 SGM-HP 50 OP

Part no...:10.01.17.00562

<https://www.schmalz.com/10.01.17.00562>

Accessories



HTR-UNI 2N X3

Part no...:10.01.03.00302

Suction cup connection: ball head 28.5 mm

Operating temperature: °C

Cross-beam connection: 2 T-slots