

Compact ejector

SEM-C 25 SDA NC AS

Part no...:10.02.02.03203

<https://www.schmalz.com/10.02.02.03203>

Home > Compact Ejectors SEM-C > SEM-C 25 SDA NC AS

Multi-stage ejector (controllable) with high suction capacity



Size: 25

Add. function: Axial silencer

Suction rate (max.): 338 l/min


Air consumption suction: 100 l/min

Max. vacuum: -870 mbar

Control valve: Normally closed

construction shape compact ejectors: With blow-off system

Design Data



Attribute	Value
B	94.50 mm
B1	170 mm
d	5.50 mm
D1	40 mm
G1	G1/4"-F
G2	G1/2"-F
G3	G1/2"-F
H	70 mm
L	199.50 mm
L1	279.50 mm
L2	10.50 mm
X1	183 mm
Y1	55 mm

Technical Data

Attribute	Value
Suction rate (max.)	338 l/min
Degree of evacuation	87 %
Air consumption suction	100 l/min
Control valve	Normally closed
Weight	1.64 kg

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Compact ejector

SEM-C 25 SDA NC AS

Part no...:10.02.02.03203

<https://www.schmalz.com/10.02.02.03203>


Operating temperature 0 ... 50 °C

Size 25

Product family SEM-C

Note: Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

Accessories



ASK B-Form-C 5000 K-3P

Part no...:21.04.06.00084

Electrical connection: Fem connect Form C

Cable length: 5,000 mm

Material hose: PVC cable

Spare parts



SD G1/2-AG 40x80 SEM

Part no...:10.02.01.00309

Thread G1: G1/2"-M

External diameter D: 40 mm

Length L: 80 mm

Construction use: Multi-stage ejectors