

Flat suction cup (round)

SGA 16 SI-55 N029

Part no.:10.01.01.00452

<https://www.schmalz.com/10.01.01.00452>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Different Industries > SGA 16 SI-55 N029

Flat suction cup (round)




Size: 16

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	9 mm
d1	12 mm
Dk	16 mm
Dmax(S)	17.50 mm
Ds	15 mm
H	12 mm
H2	2 mm
H3	4 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Size	16
Suction cup material	Silicone SI
Suction force (-600mbar)	6.90 N
Material hardness [Shore A]	55 Shore A
Volume	0.61 cm ³
Curve radius (min) (convex)	15 mm
Number of folds	0

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SGA 16 SI-55 N029

Part no...:10.01.01.00452

<https://www.schmalz.com/10.01.01.00452>

Weight	1.10 g
Product family	SGA

Accessories



SA-NIP N029 G1/8-AG DN350

Part no...:10.01.01.00816

Thread G1: G1/8"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N029 G1/8-IG DN350

Part no...:10.01.01.00815

Thread G1: G1/8"-F

Fitting length: 13 mm

Material: Aluminum

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl