

Bell suction cup (round)

SAXM 30 ED-85 G1/4-AG

Part no.:10.01.19.00049

<https://www.schmalz.com/10.01.19.00049>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Bell-Shaped Suction Cups SAXM > SAXM 30 ED-85 G1/4-AG

Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 30


Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

Design Data



Attribute	Value
dn	5.10 mm
Dmax(S)	35.20 mm
Ds	31.60 mm
G1	G1/4"-M
H	25 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	4.30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	39 N
Lateral force	32 N
Lateral force (oily surface)	41 N
Volume	3.40 cm ³
Curve radius (min) (convex)	18 mm
Hose diameter (rec.) d	5 mm
Size	30

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bell suction cup (round)

SAXM 30 ED-85 G1/4-AG

Part no.:10.01.19.00049

<https://www.schmalz.com/10.01.19.00049>

Connection	G1/4"-M
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	85 Shore A
Weight	14.50 g
Product family	SAXM

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SC-A 045 G1/4-AG L

Part no.:10.01.06.02818

Connection geometry: 045

Thread G1: G1/4"-M

Fitting length: 7.2 mm

Shape: Self Locking



SAXM 30 ED-85 SC045

Part no.:10.01.19.00004

Size: 30

Suction cup material: Elastodur ED

Material hardness [Shore A]: 85 Shore A

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Bell suction cup (round)

SAXM 30 ED-85 G1/4-AG

Part no...:10.01.19.00049

<https://www.schmalz.com/10.01.19.00049>



SC-S 045 FDC-L

Part no...:10.01.06.02803

Shape: Frict elem with Self lock