

Flat suction cup (round)

SAF 30 HT2-65 G1/4-AG

Part no.:10.01.01.12349

<https://www.schmalz.com/10.01.01.12349>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for High-Temperature Applications > Flat Suction Cups SAF HT2 > SAF 30 HT2-65 G1/4-AG

Flat suction cup (round) for very dynamic handling



Size: 30

Suction cup material: High temperature material HT2


Material hardness [Shore A]: 65 Shore A

Temperature resistance: 200 °C

Nipple material: Aluminum

Connection: G1/4-AG

Design Data



Attribute	Value
dn	4 mm
Ds	31 mm
Dmax(S)	34 mm
G1	G1/4"-M
H	20 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	3 mm

Technical Data

Attribute	Value
Number of folds	0
Size	30
Suction force (-600mbar)	38 N
Temperature resistance	200 °C
Product family	SAF

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SAF 30 HT2-65 G1/4-AG

Part no.:10.01.01.12349

<https://www.schmalz.com/10.01.01.12349>

Accessories



SU 30

Part no.:10.01.01.12889

Size: 30

Clamping range: 27.0 ... 35.0 mm

Temperature resistance: 80 °C