

Suction plate (round)

SPL-HT 60 ST G1/4-IG

Part no.: 10.01.23.00006

<https://www.schmalz.com/10.01.23.00006>

Home > Suction Plates for High-Temperature SPL-HT > SPL-HT 60 ST G1/4-IG

Suction plate for high-temperature applications




Size: 60

Suction cup material: Silicate fabric ST

Connection: G1/4-IG

Working temperature max.: 600 °C

Design Data



Attribute	Value
dn	7 mm
Dmax(S)	79.50 mm
Ds	58 mm
G1	G1/4"-F
H	39 mm
LG1	12 mm
SW1	17 mm
SW2	8 mm
SW3	27 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	130 N
Volume	12 cm ³
Curve radius (min) (convex)	440 mm
Evacuation rate for pu = -0,6 bar	32 l/min
Hose diameter (rec.) d	6 mm
Size	60
Working temperature max.	600 °C
Suction cup material	Silicate fabric ST
Weight	375 g

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Suction plate (round)

SPL-HT 60 ST G1/4-IG


Part no...:10.01.23.00006

<https://www.schmalz.com/10.01.23.00006>

Product family

SPL-HT

Spare parts




DR-SPL-HT 60 ST

Part no...:10.01.23.00001

Size: 60

Suction cup material: Silicate fabric ST



DR-SPL-HT 60 ST

Part no...:10.01.23.00001

Size: 60

Suction cup material: Silicate fabric ST