

Flat suction cup (round)


SGP 35 NK-40 N034

Part no.:10.01.01.00788

<https://www.schmalz.com/10.01.01.00788>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > SGP 35 NK-40 N034

Flat suction cup (round) for careful gripping of paper, plastic film, etc.




Size: 35

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Design Data



Attribute	Value
d	10 mm
Dk	16.50 mm
Dmax(S)	35 mm
Ds	30.20 mm
H	23.50 mm
H2	14.80 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	31 N
Volume	2.80 cm ³
Size	35
Nipple family	N 034
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Flat suction cup (round)

SGP 35 NK-40 N034

Part no...:10.01.01.00788

<https://www.schmalz.com/10.01.01.00788>

Weight	6.40 g
Product family	SGP

Accessories



SA-NIP N034 G1/4-AG DN550

Part no...:10.01.01.00820

Thread G1: G1/4"-M

Fitting length: 5 mm

Material: Aluminum



SA-NIP N034 G1/4-IG DN550

Part no...:10.01.01.00819

Thread G1: G1/4"-F

Fitting length: 15 mm

Material: Aluminum

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl