

Solenoid valve

EMV 5 24V-DC 3/2 NO

Part no.:10.05.01.00068

<https://www.schmalz.com/10.05.01.00068>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Solenoid Valves > Solenoid Valves EMV > EMV 5 24V-DC 3/2 NO

Solenoid valve EMV for direct control of vacuum and compressed air



Nominal size: 5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve


Control valve: Normally open

Connecting thread: G1/4"-F

Pressure range (operating pressure): bar

Power consumption DC: 8 W

Design Data



Attribute	Value
B	32 mm
D	56 mm
G1	G1/4"-F
G2	G1/4"-F
G3	G1/4"-F
G5	M4-F
H	71 mm
H1	118 mm
L	46 mm
L1	76 mm
LG5	4.80 mm
X1	38 mm
Y1	24 mm

Technical Data

Attribute	Value
Nominal size	5 mm
Control valve	Normally open
Nominal flow rate	66.70 l/min
Nominal flow rate	4 m ³ /h

Contact Schmalz

Schmalz Sp.z.o.o. | ul. Fabianowska 131/A1, 62-052 Komorniki, Poland | +48 61 628 67 70 | schmalz@schmalz.pl

Solenoid valve

EMV 5 24V-DC 3/2 NO

Part no.:10.05.01.00068

<https://www.schmalz.com/10.05.01.00068>

Power consumption DC	8 W
Voltage DC	24V - DC
Closing time	20 ms
Weight	0.52 kg
Product family	EMV

Accessories



FAS 63x19 G1/4-AG


Part no.:10.05.01.00060

External diameter D: 63 mm

Length L: 19 mm

Thread G1: G1/4"-M

Spare parts



FAS 63x19 G1/4-AG

Part no.:10.05.01.00060

External diameter D: 63 mm

Length L: 19 mm

Thread G1: G1/4"-M